

Aidalarm - Stainless Steel Disabled Toilet Alarm Kits

A600FKITR, A600FKITRD

The Stainless Steel, flush mount Disabled Person Toilet Alarm has been designed for more prestigious locations. It is fully compliant with BS8300 and meets the requirements of the Disability Discrimination Act. Everything is provided in the kit to deliver an effective, fully compliant, simple to install and simple to use system.

How the Aidalarm Works

- The Aidalarm controller should be installed near staff who can respond to emergency calls.
- A ceiling pull cord, optional dado panic strip, or call buttons are located in the WC or other areas where help may be needed.
- Activating the cord, button or panic strip triggers an immediate audible/visual alarm at the WC and control panel. An LED on the pull cord reassures the caller the alert was sent.
- The call can be silenced via the button on the control panel.
- Audible indicators at the WC bleep every 5 seconds to reassure the caller.
- Pulling the cord again during silence reactivates the call.
- If unattended, the panel bleeps every 40 seconds as a warning.
- The system can only be reset using the "Press to Reset" button near the call point.

**Features and Benefits**

- DDA & BS8300 Compliant
- High power piezo sSounder
- 12 vdc powered
- Audible & visual signalling
- Range of accessories
- Remote signalling output
- Manufactured in the UK
- UKCA and CE marked, ROHS compliant

Please note: The controller requires a separate 12vdc PSU minimum of 250mA, see Part No. PSU-12/2AB, if battery backup is required see Part No. BAT12V3300LA.

Kit Contents

A600FKITR - Flush Mount Aidalarm c/w S1600-R Ceiling Pull Cord, S1708SL Reset Button, S1778SR over door indicator & sounder.

A600FKITRD - Flush Mount Aidalarm c/w S1600-R Ceiling Pull Cord, S1708SL Reset Button, S1778SR over door indicator & sounder, RPD01000 Panic Strip.

**Optional Accessories**

S1705S



S0610-38

Dimensions

Facia - 180 x 125 x 2mm
Bespoke Back Box - 164 x 100 x 55mm

